

5/6 inch retrofit downlight 8.3W

Bring human-centric lighting into your life with this smart WiZ LED tunable white downlight. Easily install into existing recessed cans (aka pot lights) and apply different shades of warm to cool white to help you focus or relax. You can set schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.


PRODUCT HIGHLIGHTS

- Tunable white
- Fits 5"/6" opening
- IP20/Round/White



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



SPECIFICATIONS

BULB CHARACTERISTICS

Dimmable: Yes

DESIGN AND FINISHING

Color: White

Material: Metal Plastic

DURABILITY

Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable

Dimmable with remote control: Yes

LED integrated: Yes

Remote control included: No

Solar Energy: No

Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Beam angle: 110

Color rendering index (CRI): ≥ 90

Color temperature: 2700-5000 K

Luminous Efficacy (rated) (Nom): 72

MISCELLANEOUS

Especially designed for: Kitchen

Bedroom Dining Room Living Room

POWER CONSUMPTION

Voltage: 120 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.23 kg

Overall height: 71 mm

Overall length: 188 mm

Overall width: 188 mm

SERVICE

Warranty: 3 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 188 mm

Total lumen output fixture: 750

Bulb technology: LED

Light color: Tunable white light

Mains power: 120 V

Wattage bulb included: 8.3

Class of protection: UL non-earthed

UL Wet/ damp/ dry location: Damp location

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: 802.11b/g/n

Defined support period: Minimum of 60 months after introduction date

Max. number of accessories: 9999

Compatible operating systems: iOS
Android

Communication protocol: Bluetooth
WiFi (2.4GHz)

Compatibility with 3rd party systems:

Alexa Enki Google Home Homey

IFTTT Matter Samsung Smartthings

Siri Shortcuts

Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677556129

Net weight: 0.22 kg

Gross weight: 0.36 kg

Height: 23.4 cm

Length: 8.9 cm

Width: 21.1 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.