

# PHILIPS

Spot 20W MR11 GU4

LED

3000K

215lm

25000h

046677566548



## Long lasting LED light with a focused bright beam

Philips LED MR11 spot light bulbs are a perfect replacement for halogen spots. They have a warm halogen-like light with the performance and long life you expect from LED. Ideal for accent lighting in recessed and track lighting fixtures.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as halogen reflector

### **Choose for a sustainable solution**

- You can trust what the Philips packaging is saying.

### **Light beyond illumination**

- Instant on

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Instant on

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU4
- Dimmable: No

## Bulb dimensions

- Height: 3.95 cm
- Width: 3.55 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 35 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 215 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 82 lm/W

## Packaging information

- EAN: 046677566548
- EOC: 566547
- Product title:  
2.6MR11/LED/830/F35/ND/G/12V  
6/IPF

## Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 2.6 W
- Wattage equivalent: 20 W

## Product dimensions and weight

- Length: 3.95 cm

## Rated values

- Rated peak intensity: 400 cd

## Technical specifications

- Frequency: - Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677566548
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4 cm
- Width: 7.6 cm
- Material number (12NC):  
929002066515



Issue date: 2024-06-14  
Version: 0.58

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)