

PHILIPS

Spot 20W MR11 GU4

LED

3000K

215lm

25000h

046677566548



Long lasting LED light with a focused bright beam

Philips LED MR11 spot light bulbs are a perfect replacement for halogen spots. They have a warm halogen-like light with the performance and long life you expect from LED. Ideal for accent lighting in recessed and track lighting fixtures.

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant on

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU4
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 35 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 215 lm
- Warm-up time to 60% light: 0.5
- Color Code: 830 | CCT of 3000K
- Luminous Efficacy (rated) (Nom): 82 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 046677566548
- EOC: 566547
- Product title: 2.6MR11/LED/830/F35/ND/G/12V 6/1PF

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage equivalent: 20 W
- Power Consumption: 2.6 W

Product dimensions and weight

- Overall height: 39.5 mm
- Overall length: 39.5 mm
- Overall width: 35.5 mm

Rated values

- Rated peak intensity: 400 cd

Technical specifications

- Frequency: -

Packaging dimensions and weight

- EAN/UPC - product: 046677566548
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4 cm
- Width: 7.6 cm



Issue date: 2025-08-30
Version: 0.75

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com