



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

• True incandescent-like warm white light

Designed to be seen, looks good on and off

· Classic glass LED

Highlights

True incandescent-like warm white light



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

Intended use: Indoor/OutdoorLamp shape: Non directional bulb

Socket: E26Bulb Finish: ClearDimmable: Yes

Durability

Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

lm/W

• Beam angle: 300 degree(s)

Color rendering index (CRI): 90

• Color temperature: 2700 K

Nominal luminous flux: 400 lm

 Warm-up time to 60% light: instant full light

Color Code: 927 | CCT of 2700KLuminous Efficacy (rated) (Nom): 90

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

· Extra Features: Dimmable, Decorative

Packaging information

. EAN: 046677574284

• EOC: 574285

· Product title:

4.4ST19/VIN/927/CL/G/E26/DIM

4/2PF T20

Power consumption

Power factor: 0.7Voltage: 120 V

Wattage equivalent: 40 WPower Consumption: 4.4 W

Product dimensions and weight

Overall height: 137 mmOverall length: 137 mmOverall width: 64 mm

Technical specifications

• Frequency: 60

Packaging dimensions and weight

• EAN/UPC - product: 046677574284

Net weight: 0.09 kgGross weight: 0.15 kgHeight: 20.4 cm

Length: 7.1 cmWidth: 15.6 cm



Issue date: 2025-11-01 Version: 0.84 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V