

PHILIPS

Filament Candle Clear
40W B11 E26 x3

LED

5000K

300lm

15000h

Dimming

046677574345



Bright LED lighting with excellent light quality

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E26) fittings.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: B11
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 5000 K
- Nominal luminous flux: 300 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K
- Luminous Efficacy (rated) (Nom): 85 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Packaging information

- EAN: 046677574345
- EOC: 574343
- Product title: 3.5B11/PER/UD50/CL/G/E26/D 4/3CT T20

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage equivalent: 40 W
- Power Consumption: 3.5 W

Product dimensions and weight

- Overall height: 90 mm
- Overall length: 90 mm
- Overall width: 35 mm

Technical specifications

- Frequency: 60

Packaging dimensions and weight

- EAN/UPC – product: 046677574345
- Net weight: 0.06 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 13 cm



Issue date: 2025-08-30
Version: 0.43

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com