



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

High quality light

Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Light beyond illumination

• Dims to a warm glow

High quality LED light that lasts for decades

· Light that shows true colors

Designed to be seen, looks good on and off

· Classic glass LED

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light..

Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe - you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

· Intended use: Indoor/Outdoor · Lamp shape: Non directional bulb

· Socket: E26 · Dimmable: Yes · Bulb Finish: Clear · Bulb Material: Glass

Durability

Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Beam angle: 300 degree(s)

· Color rendering index (CRI): 95

· Color temperature: 2200-2700 K

· Nominal luminous flux: 800 lm

• Warm-up time to 60% light: instant full light

· Color Code: 927-922 | CCT of

2700K-2200K

· Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

• Extra Features: Dimmable, WarmGlow

Packaging information

. EAN: 046677574437

• EOC: 574434

· Product title:

8A19/PER/UD/CL/G/E26/

WGD4/2PFT20

Power consumption

• Energy Star Certified: No

Power factor: 0.7Voltage: AC 120 V

Wattage equivalent: 60 WPower Consumption: 8 W

Product dimensions and weight

Overall height: 10.5 mmOverall length: 10.5 mmOverall width: 6 mm

Technical specifications

• Frequency: 60

can it be used in closed luminaires:No

Packaging dimensions and weight

• EAN/UPC - product: 046677574437

Net weight: 0.07 kgGross weight: 0.08 kg

Length: 6.5 cmWidth: 13 cm

· Height: 17.1 cm



Issue date: 2025-11-01 Version: 0.95 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips