



# Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes

# Easy to experience

· Easy installation

# Light effect

· Bright light with uniform distribution

#### **Premium quality**

• EyeComfort - light that's easy on the eyes

#### Control

• Dimmable

# Highlights

#### **Easy installation**

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

#### Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

#### **Eyecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that

way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

#### **Dimmable**

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

Lamp shape: RoundRectangle

#### Design and finishing

Color: WhiteMaterial: Plastic

# **Durability**

- Average life (at 2.7 hrs/day): 51 year(s)
- · Lumen maintenance factor: 70%
- Number of switch cycles: 25,000
- · Nominal lifetime: 50,000

# **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

#### **Light characteristics**

- · Color consistency: 6 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 5000 K
- · Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 75 lm/W

#### Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Garage
- Style: Contemporary
- · Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable

#### Other characteristics

· Lamp current: 238 mA

# Power consumption

• Power factor: 0.7

#### Product dimensions and weight

- · Net weight: 0.36 kg
- Overall height: 62 mm
- · Overall length: 280 mm
- · Overall width: 280 mm

#### **Service**

Warranty: 3 year(s)

# **Technical specifications**

· Diameter: 280 mm

• Total lumen output fixture: 1500

Light color: 5000Mains power: AC 120Fixture dimmable: Yes

IP code: ULO2 | Damp LocationClass of protection: UL earthed

# Packaging dimensions and weight

• EAN/UPC - product: 046677574505

Net weight: 0.36 kgGross weight: 0.64 kg

Height: 33 cmLength: 7.8 cmWidth: 32.5 cm



Issue date: 2025-11-01 Version: 0.169 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V