



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

High quality light

Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

Intended use: Indoor/OutdoorLamp shape: Non directional bulb

Socket: E26Dimmable: YesBulb Finish: ClearBulb Material: Glass

Durability

· Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

Beam angle: 300 degree(s)Color rendering index (CRI): 95

· Color temperature: 2200-2700 K

· Nominal luminous flux: 450 lm

 Warm-up time to 60% light: instant full light

 Color Code: 927-922 | CCT of 2700K-2200K

Luminous Efficacy (rated) (Nom): 90 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

 Extra Features: Dimmable, WarmGlow

Packaging information

• EAN: 046677575045

• EOC: 575043

Product title: 5A15/PER/

UD50/CL/G/E26/WGD 4/1PF T20

Power consumption

Power factor: 0.7Voltage: 120 V

Wattage equivalent: 40 WPower Consumption: 5 W

Product dimensions and weight

Overall height: 84 mmOverall length: 84 mmOverall width: 47.5 mm

Technical specifications

• Frequency: 60

Packaging dimensions and weight

• EAN/UPC - product: 046677575045

Net weight: 0.04 kgGross weight: 0.05 kgHeight: 14.6 cm

Length: 5.5 cmWidth: 7.5 cm



Issue date: 2025-11-01 Version: 0.43 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips