

PHILIPS

Filament Bulb
Frosted 60W A19 E26

LED

5000/2700/3000/3500/4000
K

800lm

15000h

Dimming

046677580186



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose a simple replacement for your old bulbs

- Perfect fit and high-quality finishing

Highlights

Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Dimmable: Only with specific dimmers
- Bulb Finish: Frosted
- Bulb Material: Glass

Bulb dimensions

- Height: 11 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 5000/2700/3000/3500/4000 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light
- Color Code: 5000/2700/3000/3500/4000

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 114 lm/W

Packaging information

- EAN: 046677580186
- EOC: 580183
- Product title: 7A19/WhiteD/5CCT/FR/G/E26/D 4/1PF T20 CA

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 7 W
- Wattage equivalent: 60 W

Product dimensions and weight

- Length: 11 cm

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677580186
- Net weight: 0.04 kg
- Gross weight: 0.07 kg
- Height: 17.1 cm
- Length: 6.6 cm
- Width: 7.6 cm
- Material number (12NC): 929003126805



Issue date: 2024-07-25
Version: 0.61

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com