



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose a simple replacement for your old bulbs

· Similar shape and size as standard incandescent bulb

Highlights

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: E26dDimmable: NoBulb Finish: FrostedBulb Material: Plastic

Durability

Number of switch cycles: 50,000Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 250 degree(s)

· Color rendering index (CRI): 90

· Color temperature: 5000 K

• Nominal luminous flux: 2150, 1600, 620 lm

 Warm-up time to 60% light: instant full light

· Color Code: 5000K

 Luminous Efficacy (rated) (Nom): 116 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

Packaging information

• EAN: 046677580193

• EOC: 580191

· Product title:

18.5A21/PER/950/FR/P/ E26/3WAY/T20 4/1PF

Power consumption

· Power factor: 0.7

· Voltage: 120 V

Wattage equivalent: 150;100;50 W
Power Consumption: 18.5, 13, 6 W

Product dimensions and weight

· Overall height: 133.1 mm

· Overall length: 133.1 mm

· Overall width: 70.6 mm

Technical specifications

• Frequency: 60

 UL Wet/ damp/ dry location: Damp location

• can it be used in closed luminaires:

Packaging dimensions and weight

• EAN/UPC - product: 046677580193

· Net weight: 0.14 kg

· Gross weight: 0.19 kg

· Height: 20.4 cm

• Length: 7.5 cm

· Width: 8 cm



Issue date: 2025-11-01 Version: 0.88

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips