



Bright LED lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. Select desired color temperature via switch before installing the LED tube.

Choose a simple replacement for your old bulbs

Double-Ended Installation

Choose for a sustainable solution

· Long life bulb - Lasts up to 50 years

Highlights

MainsFit Double-Ended

Philips MainsFit LED tubes are doubleended and can be installed in either direction.

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: T8Socket: G13

Bulb Finish: FrostedDimmable: YesBulb Material: Glass

Durability

Number of switch cycles: 50,000Nominal lifetime: 50,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Beam angle: 240 degree(s)

· Color rendering index (CRI): 80

· Color temperature:

3000-3500-4000-5000-6500 K

Nominal luminous flux: 1800 lm

· Warm-up time to 60% light: 0.5

 Color Code: 3000K/3500K/4000K/ 5000K/6500K

 Luminous Efficacy (rated) (Nom): 124 lm/W

Miscellaneous

· EyeComfort: No

• Extra Features: Dimmable

Packaging information

• EAN: 046677580216

• EOC: 580217

Product title: 14.5T8/LED/48-5CCT/ MF18/G/DIM 5/2 FB

Power consumption

Power factor: 0.9Voltage: 120-277 V

Wattage equivalent: 32 WPower Consumption: 14.5 W

Product dimensions and weight

Overall height: 1,212.3 mm
Overall length: 1,212.3 mm
Overall width: 27.8 mm

Service

Warranty: 5 year(s)

Technical specifications

• Frequency: VA5358160

Packaging dimensions and weight

• EAN/UPC - product: 046677580216

· Net weight: 0.4 kg

· Gross weight: 0.57 kg

Height: 122.5 cm

· Length: 6.1 cm

• Width: 3.1 cm



Issue date: 2025-11-01 Version: 0.65 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V