

PHILIPS

6 inch Recessed
Light 11.5W


Recessed Lights

2700/3000/3500/4000/5000
K

White

Dimmable

046677580391



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Match your interior

- Super slim design

Light effect

- Adjustable color temperature
- Uniform light distribution

Premium quality

- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 25,000 hours

Highlights

Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

Adjustable color temperature

Shift seamlessly from cool white light for concentration to a more cozy glow to unwind in.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan,

delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Metal

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 12,500

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: <4 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable

Other characteristics

- Lamp current: 110 mA
- Efficacy: 86 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 0.4 kg
- Cut out length: 16.0 cm
- Cut out width: 16.0 cm
- Height: 2.4 cm
- Length: 17 cm
- Recessed distance: 0 cm
- Width: 17 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Diameter: 170 mm
- Total lumen output fixture: 1000
- Light color: 2700/3000/3500/4000/5000
- Mains power: 120
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 11.5
- IP code: UL02 – Damp Location (North America)
- Class of protection: UL earthed

Packaging dimensions and weight

- EAN/UPC – product: 046677580391
- Net weight: 0.4 kg
- Gross weight: 0.48 kg
- Height: 17.6 cm
- Length: 6.7 cm
- Width: 17.5 cm
- Material number (12NC): 929003259603



Issue date: 2024-04-25
Version: 0.102

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com