



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Easy to experience

· Hassle-free installation that does not require wiring.

Light effect

- Adjustable color temperature
- · Uniform light distribution

Premium quality

• EyeComfort - light that's easy on the eyes

Durability

· Long life span up to 25,000 hours

Highlights

Easy installation

Adjustable color temperature

Shift seamlessly from cool white light for concentration to a more cozy glow to unwind in.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver

comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Plastic

Durability

Average life (at 2.7 hrs/day): 25 year(s)

• Lumen maintenance factor: 70%

• Number of switch cycles: 12,500

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

Adjustable spot head: No

• Dimmable with remote control: No

LED integrated: Yes

· Remote control included: No

Light characteristics

• Beam angle: 100 degree(s)

Color consistency: <4 SDCM

· Color rendering index (CRI): 90

• Warm-up time to 60% light: <2

Miscellaneous

 Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office

• Style: Contemporary

• Type: Recessed Lights

 $\bullet \ \, \text{EyeComfort: Yes}$

• Extra Features: Dimmable

Other characteristics

• Lamp current: 110 mA

• Efficacy: 95 lm/W

Power consumption

• Power factor: 0.7

Product dimensions and weight

· Net weight: 0.24 kg

Height: 7.4 cm

• Length: 19 cm

• Width: 19 cm

Service

Warranty: 3 year(s)

Technical specifications

Lifetime up to: 25,000 hour(s)

· Diameter: 190 mm

• Total lumen output fixture: 1000

• Light color:

2700/3000/3500/4000/5000

· Mains power: 120

· Fixture dimmable: Yes

· LED: Yes

• Wattage bulb included: 10.5

 $\boldsymbol{\cdot}$ IP code: UL02 - Damp Location

(North America)

· Class of protection: UL non-earthed



Issue date: 2024-07-30 Version: 0.122 © 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V