

# PHILIPS

Reflector 50W  
PAR20 E26 x3

LED

3000

505lm

25000

Dimming

046677587208



## Dimmable LED spot with excellent light quality

Philips dimmable LED PAR spot light lamps are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Instant on

**Designed for the comfort of your eyes**



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 3000 K
- Nominal luminous flux: 505 lm
- Luminous Efficacy (rated) (Nom): 87 lm/W

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Packaging information

- EAN: 046677587208
- EOC: 587204
- Product title: 5.8PAR20/PER/UD/30/G/E26/F40/D /T 4/3CT

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 50 W
- Power: 5.8 W

**Product dimensions and weight**

- Overall height: 83 mm
- Overall length: 83 mm
- Overall width: 64 mm

**Rated values**

- Rated peak intensity: 593 cd

**Packaging dimensions and weight**

- EAN/UPC - product: 046677587208
- Net weight: 0.36 kg
- Gross weight: 0.46 kg
- Height: 12.1 cm
- Length: 7 cm
- Width: 15.5 cm

**Technical specifications**

- Frequency: 50-60



Issue date: 2026-01-31  
Version: 0.127

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)