



# Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

# High quality light

Designed for the comfort of your eyes

## Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

#### High quality LED light that lasts for decades

· Light that shows true colors

# Designed to be seen, looks good on and off

· Classic glass LED

# Dimmable (LED Lamps)

· Dimmable (LED Lamps)

# Highlights

# Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

# **Glass Frosted Design**

The look you love, the performance you expect. Classic frosted glass designs that replicate the soft glowing light of traditional bulbs, for a perfect fit throughout your home.

# Dimmable (LED Lamps)



This lamp can be used with most dimmers to create your desired ambience with smooth dimming. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this lamp.

# Specifications

#### **Bulb characteristics**

Intended use: Indoor/OutdoorLamp shape: Non directional bulb

· Socket: E26

Bulb Finish: FrostedDimmable: YesBulb Material: Glass

## **Durability**

· Number of switch cycles: 20,000

· Nominal lifetime: 15,000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# **Light characteristics**

Beam angle: 300 degree(s)Color rendering index (CRI): 95

Color temperature: 5000 KNominal luminous flux: 1500 lm

Luminous Efficacy (rated) (Nom): 130 lm/W

#### Miscellaneous

• EyeComfort: Yes

• LED Innovations: EyeComfort

· Extra Features: Dimmable

#### **Packaging information**

• EAN: 046677587659

• EOC: 587659

 Product title: 11.5A19/PER/ UD50/FR/G/E26/D 4/1PF T20

#### **Power consumption**

· Energy Star Certified: No

Power factor: 0.7Voltage: AC 120 V

Wattage equivalent: 100 WPower Consumption: 11.5 W

## Product dimensions and weight

Overall height: 10.5 mmOverall length: 10.5 mm

• Overall width: 6 mm

#### **Rated values**

· Rated peak intensity: 130 cd

# **Technical specifications**

• Frequency: 60

can it be used in closed luminaires:
Yes

#### Packaging dimensions and weight

• EAN/UPC - product: 046677587659

Net weight: 0.04 kgGross weight: 0.06 kg

Height: 17.1 cmLength: 7.5 cmWidth: 6.5 cm



Issue date: 2025-11-05 Version: 0.146 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.