



046677590048



Enjoy a Beautiful garden with light, in a sustainable way

Philips Ashlyn is a reliable solar light that lasts longer time, reduces energy consumption and supports sustainability.

Easy installation

No wiring requried

Sustainable light solutions

- Solar energy
- · Long lifetime up to 25,000 hours

Advanced LED light

· High quality LED light

Premium quality

· High quality material

Designed for outdoors

· IP44 - weather proof

High quality light

· Bright white light 3000K

Highlights

No wiring requried



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Solar energy



Philips Solar lights are designed to make the most of the energy they receive from the sun, for light that lasts longer. With no electricity consumption at all, it helps you save money on your electricity bills and do your bit for the environment.

Long lifetime up to 25,000 hours



Reliable high-quality LED light lasts up to 25,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

High quality material



This Philips outdoor lamp is made of high quality materials with superior finishing. This ensures a solid and long lasting product which is resistant to corrosion and stains in all weather conditions

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Bright white light 3000K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces bright white light at 3000 K.

Specifications

Design and finishing

Color: BlackMaterial: Plastic

Durability

· Nominal lifetime: 25,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

· Adjustable spot head: Not adjustable

· Anti rust anti dust: Yes

· Bi-directional light beams: No

· Day-and-night sensor: Yes

• Fully weatherproof: Yes

· LED integrated: Yes

• Motion sensor: No

· Solar Energy: Yes

· Centerpiece: No

Light characteristics

Beam angle: 120 degree(s)Color rendering index (CRI): 80Color temperature: 3000 K

Miscellaneous

• Especially designed for: Garden, Patio

• Style: Contemporary

Type: Ground Spots/Spikes

Power consumption

• Power Consumption: 1

Product dimensions and weight

Net weight: 0.35 kgOverall height: 350 mm

Service

Warranty: 3 year(s)

Technical specifications

· Total lumen output fixture: 100

Light color: 3000Mains power: DC 4Fixture dimmable: No

IP code: UL03 | Wet LocationClass of protection: Class III - Safe

Extra Low Voltage

Light source replaceable: NoNumber of light sources: 1

UL Wet/ damp/ dry location: Wet location

Packaging dimensions and weight

• EAN/UPC - product: 046677590048

Net weight: 0.35 kgGross weight: 0.48 kgHeight: 21.5 cmLength: 11.5 cm

· Width: 15 cm



Issue date: 2025-11-01 Version: 0.115 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.