

PHILIPS

Spot 50W PAR16
GU10 x3

LED

2700-2200K

400lm

25000h

Dimming

046677590703



Dimmable LED spot with a focused bright beam

Not all LEDs dim the same. Philips dimmable LED MR16 spot light bulbs with a warm glow effect work like halogen bulbs by getting warmer in tone when dimmed. Other LED bulbs simply get less bright, without the cozy glow.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Light beyond illumination

- Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 35
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Nominal luminous flux: 400 lm
- Luminous Efficacy (rated) (Nom): 100

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 046677590703
- EOC: 590703
- Product title: 4GU10/LED/UD27-22/F35/G/WG/3CT

Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 50
- Power: 4

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 600 cd

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- can it be used in closed luminaires:
Yes

Packaging dimensions and weight

- EAN/UPC - product: 046677590703
- Net weight: 0.13 kg
- Gross weight: 0.16 kg
- Height: 12.2 cm
- Length: 5.6 cm
- Width: 13.1 cm



Issue date: 2026-03-21
Version: 0.89

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com