PHILIPS

hue

Starter kit: 4 E26 color-capable bulbs + Bridge Pro

Hue White and color ambiance

Supports 150+ lights, 50+ accessories

MotionAware™ technology

White ambiance +16 million colors

Advanced encryption with Zigbee Trust Center



046677591908



Easy smart lighting

Get superpowered smart lighting features with the Bridge Pro. Equipped with a new chip capable of running complex algorithms and AI-powered features, it's faster and stronger than ever. Add ambient color to any room with the included color-capable bulbs.

Limitless possibilities

- Whole-home control from anywhere
- Hue MotionAware™
- More capacity, faster processor


Easy smart lighting

- Zigbee security

Issue date: 2026-07-11 Version: 0.72


Highlights

Whole-home control from anywhere



The Bridge and Bridge Pro give you access to your smart home system from anywhere via the Hue app. Control your lights, receive security notifications — or just set up your system to run on a schedule with automations.

Hue MotionAware™




This exciting new feature exclusive to Bridge Pro empowers your lighting system to intuitively respond to your movements around the home. Using at least 3 lights in the same room, you can create a motion area that detects your presence and triggers any lights you assign to it. No separate motion sensor needed!

More capacity, faster processor

Compared with Bridge, the Bridge Pro brings 3x more capacity, support for 150+ lights, 50+ accessories, 500 scenes, plus 5x faster response times with its new Hue Chip Pro.

Zigbee security



Your privacy is our priority. Zigbee and Philips Hue prevent unauthorized access to your smart light ecosystem.

Specifications

Bulb dimensions
- Dimensions (WxHxD): 62 x 112

Design and finishing
- Color: Black
- Material: Synthetic

Durability
- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 25,000

Environmental
- Operational humidity: 0%<H<80% (non condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.
- Dimmable with Hue app and switch: Yes
- Hue bridge included: Yes

Guarantee
- 3 years: Yes

Light characteristics
- Color rendering index (CRI): >80
- Color temperature: 1000-20000 K

Packaging information
- EAN: 046677591908

Power consumption
- Standby power consumption: 0.1 W
- Power: 9.5 W

Service
- Warranty: 3 year(s)

Technical specifications
- Lumen output at 4000K: 1,100
- Diameter: 62 mm
- Bulb technology: LED
- Fitting/cap: E26
- IP code: IP20
- Number of light sources: 4

The bridge
- Diameter: 92.3 mm
- Frequency band: 2400-2483.5 MHz
- Height: 26 mm
- Length X Width: 92.3 x 92.3 mm
- Max. number of bulbs: 150
- Mounting options: Desktop, Wall
- Power adapter: 100–240 V AC / 50–60Hz, Standby power: 0.1 W max, Output voltage: 5 V DC 1A (max)
- Height: 1 inch
- Length X Width: 3.6 x 3.6 inch

The bulb
- Form factor: A19
- Height: 112 mm
- Input voltage: 110V-130V
- Light output: White and color light
- Lumen output: 1100 lm @ 4000K
- Power factor: 0.7
- Software upgradable: Yes
- Start up: Instant 100% light output
- Wattage equivalent: 75 W
- Height: 4.4 inch
- Width: 2.4 inch
- Deep dimmable: Yes

What's in the box
- Bridge: 1
- Ethernet network cable: 1
- Hue bulbs: 4
- Power adapter: 1

What's supported
- Compatible with Effects: Yes
- Philips Hue App: Android 12.0 and above, iOS 17 or later
- Voice assistants (Hue Bridge required): Amazon Alexa, Apple Home, Google Assistant, Samsung Smartthings
- WiFi: Works without Wi-Fi
- Defined support period: Minimum 60 months, 36 months for bridge from date of purchase from an authorized reseller
- Max. number of accessories: 50
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, Zigbee
- Compatibility with 3rd party systems: Alexa, Google Home, Apple Home, IFTTT, Klikaanklikuit, Matter, Samsung Smartthings, Sonos
- Matter functionality: Via Hue Bridge

Box specifications

Packaging dimensions and weight
- EAN/UPC - product: 046677591908
- Net weight: 0.59 kg
- Gross weight: 1.01 kg
- Height: 140 mm
- Length: 176 mm
- Width: 219 mm



© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.