



LED Strip Extension 3.3ft

Extend your WiZ full color strip (starter kit sold separately) with this 1 meter extension to a maximum of 10 meters. Simply stick the flexible light strip to any surface you like. Wi-Fi connected, 16 million colors and adjustable from warm white to daylight.

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- IP20/Pu-coating



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

DESIGN AND FINISHING

Color: White
Material: Plastic

DURABILITY

Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: No
LED integrated: No
On/off switch on wire: No
Power adapter included: No
Remote control included: No

LIGHT CHARACTERISTICS

Color rendering index (CRI): ≥ 80
Color temperature: 2700-6500 K
Luminous Efficacy (rated) (Nom): 72

MISCELLANEOUS

Especially designed for: Living Room
Kitchen Bedroom Children's room

POWER CONSUMPTION

Voltage: 12 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.05 kg
Overall height: 2.2 mm
Overall length: 1,000 mm
Overall width: 12 mm

SERVICE

Warranty: 1 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 800
Light color: Coloured and white light (RGBW)
Mains power: 12
Fixture dimmable: Yes
Fixture is compatible with bulb(s) of class: A
Wattage bulb included: 11
IP code: IP20 | Finger-protected
Class of protection: UL non-earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Google Home IFTTT
Klikaanklikuit Matter Samsung Smartthings Sonos

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677603571
Net weight: 0.05 kg
Gross weight: 0.08 kg
Height: 16.2 cm
Length: 4.6 cm
Width: 7.6 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.