

Bar Linear Light

If you have a shelf or corner that needs accent lighting, try our Bar light. This slim bar radiates plenty of colors and is easy to fit in small spaces. Simply tilt it on one of its sides to adjust the light angle. Do you prefer a longer light? Connect a second bar to double the effect.

PRODUCT HIGHLIGHTS

- Full color
- Versatile bar light
- Easy plug and play




Smart lighting functionalities easy to set up
Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement
WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection.It´s simple. It´s SpaceSense. It´s WiZ.



Set up lights to follow your own schedule
Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene
Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colors and changing light modes to make your day
Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light
Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

EAN: 046677604332

wizconnected.com

SPECIFICATIONS

BULB CHARACTERISTICS
Intended use: Indoor
Lamp shape: Rectangle
Dimmable: Yes

DESIGN AND FINISHING
Color: White
Material: Plastic

DURABILITY
Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.
Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Remote control included: No
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS
Color consistency: 6 SDCM
Color rendering index (CRI): ≥80
Color temperature: 2200-6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 76

MISCELLANEOUS
Especially designed for: Bedroom Dining Room Living Room Children's room

OTHER CHARACTERISTICS
Lamp current: 150 mA

POWER CONSUMPTION
Power factor: 0.7
Voltage: 100-240 V

PRODUCT DIMENSIONS AND WEIGHT
Net weight: 0.7 kg
Overall height: 42 mm
Overall length: 600 mm
Overall width: 45 mm

SERVICE
Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS
Total lumen output fixture: 800
Bulb technology: LED
Light color: Coloured and white light (RGBW)
Wattage bulb included: 10.5
Class of protection: Class II - Double Insulated
UL Wet/ damp/ dry location: Damp location

THE BULB
Software upgradable: Yes

WHAT'S SUPPORTED
Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS Android
Communication protocol: Bluetooth WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT
EAN/UPC - product: 046677604332
Net weight: 0.7 kg
Gross weight: 0.9 kg
Height: 8.7 cm
Length: 5.9 cm
Width: 40.5 cm

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.