



## Bar Linear Light

If you have a shelf or corner that needs accent lighting, try our Bar light. This slim bar radiates plenty of colors and is easy to fit in small spaces. Simply tilt it on one of its sides to adjust the light angle. Do you prefer a longer light? Connect a second bar to double the effect.

## PRODUCT HIGHLIGHTS

- Full color
- Versatile bar light
- Easy plug and play



## Smart lighting functionalities easy to set up


Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!

## Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.

## Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



## Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.

## Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.

## Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: Rectangle  
Dimmable: Yes

## DESIGN AND FINISHING

Color: White  
Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable  
Dimmable with remote control: Yes  
LED integrated: Yes  
On/off switch on wire: No  
Remote control included: No

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI): ≥80  
Color temperature: 2200-6500 K  
Warm-up time to 60% light: 2  
Luminous Efficacy (rated) (Nom): 76  
lm/W

## MISCELLANEOUS

Especially designed for: Living Room  
Dining Room Bedroom Children's  
room

## OTHER CHARACTERISTICS

Lamp current: 150 mA

## POWER CONSUMPTION

Power factor: 0.7  
Voltage: 100-240 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.7 kg  
Overall height: 42 mm  
Overall length: 600 mm  
Overall width: 45 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Total lumen output fixture: 800  
Light color: Coloured and white light  
(RGBW)  
Wattage bulb included: 10.5  
Class of protection: Class II - Double  
Insulated  
UL Wet/ damp/ dry location: Damp  
location

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: Wireless G  
Defined support period: Minimum of  
60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth  
WiFi (2.4GHz)  
Compatibility with 3rd party systems:  
Alexa Google Home IFTTT  
Klikaanklikuit Matter Samsung  
Smarthings Sonos

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604332  
Net weight: 0.7 kg  
Gross weight: 0.9 kg  
Height: 8.7 cm  
Length: 5.9 cm  
Width: 40.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.