

LED Strip 13ft

Cut, shape, and reshape our Indoor Ambience LED Strip as you need it. Its colored, dynamic light modes beautify the space under your cabinets or behind furniture, and its ambient light creates the perfect mood when all you want is chill.

PRODUCT HIGHLIGHTS

- Full color
- Power supply unit included
- IP20/Plastic



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor

DESIGN AND FINISHING

Color: White

Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Number of switch cycles: 50,000

Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable

Dimmable with remote control: No

LED integrated: Yes

On/off switch on wire: Yes

Power adapter included: Yes

Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM

Color rendering index (CRI): ≥ 80

Color temperature: 2700-5000 K

Warm-up time to 60% light: 2

Luminous Efficacy (rated) (Nom): 66

MISCELLANEOUS

Especially designed for: Living Room

Kitchen Bedroom Children's room

OTHER CHARACTERISTICS

Lamp current: 135 mA

POWER CONSUMPTION

Power factor: 0.5

Voltage: 100-120 V

Power: 12

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.232 kg

Overall height: 3 mm

Overall length: 4,000 mm

Overall width: 10 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 840

Light color: Coloured and white light (RGBW)

Fixture dimmable: Yes

Wattage bulb included: 12.7

IP code: IP20 | Finger-protected

Class of protection: UL non-earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date

Max. number of accessories: 9999

Communication protocol: Bluetooth WiFi (2.4GHz)

Compatibility with 3rd party systems:

Alexa Google Home IFTTT

Klikaanklikuit Matter Samsung

Smartthings Sonos

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604400

Net weight: 0.22 kg

Gross weight: 0.28 kg

Height: 16 cm

Length: 5.7 cm

Width: 14.1 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.