



## Wall Light ELPAS

These weatherproof, elegantly designed mains voltage fixtures give an exciting new twist to the classic outdoor wall light. Install in your front garden, back garden, balcony, or porch for 400 lumens of beautiful light. Select from millions of colors, warm to cool whites, and dynamic light modes using your existing Wi-Fi.

## PRODUCT HIGHLIGHTS

- Full color
- Mains Voltage
- Weatherproof




### Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.




### Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



### Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.




### Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



### Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



### Control your outdoor lights the way you like it

WiZ gives you many options to control your smart lights. Simply adjust lights with your smartphone or your voice from wherever you are. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Outdoor  
Lamp shape: RoundRectangle  
Dimmable: Yes

## DESIGN AND FINISHING

Color: Black  
Material: Metal Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 25,000

## EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable  
Dimmable with remote control: Yes  
LED integrated: Yes  
LED lamp(s) included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Color consistency: 7 SDCM  
Color rendering index (CRI):  $\geq 80$   
Color temperature: 2700-5000 K  
Warm-up time to 60% light: 2  
Luminous Efficacy (rated) (Nom): 76

## MISCELLANEOUS

Especially designed for: Balcony  
Garden

## OTHER CHARACTERISTICS

Lamp current: 77 mA

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 100-120 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.705 kg  
Overall height: 198 mm  
Overall length: 159 mm  
Overall width: 117 mm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Lumen output bulb included: 950  
Diameter: 109 mm  
Total lumen output fixture: 650  
Light color: Coloured and white light (RGBW)  
Wattage bulb included: 8.5  
Maximum wattage replacement bulb: 8.5  
Class of protection: UL earthed  
Light source replaceable: No  
Number of light sources: 1  
UL Wet/ damp/ dry location: Wet location

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: 802.11b/g/n  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)  
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604448  
Net weight: 0.71 kg  
Gross weight: 0.96 kg  
Height: 23.1 cm  
Length: 13.6 cm  
Width: 19.3 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.