



Bollard Extension

Plug-and-play to extend your existing WiZ outdoor bollards installation. Low-voltage fixtures are easy and safe to install. Arrange and rearrange however you like with no additional wiring. Use your existing Wi-Fi to control the lights with your voice or the WiZ app.

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- Weatherproof




Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



Low-voltage technology and easy installation

Designed for outdoor enjoyment! No complicated wiring or special installation required—just plug it in and go. If you want to change the light's location, just unscrew the adapter and move it somewhere else.



Set a different color for each spot and amplify the mood

Let the play of dynamic light modes amplify the mood. Easily set each spot to shine a different color. Mix and match millions of light colors or a variety of light modes to create a unique light effect that fits your style.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Outdoor
Lamp shape: Round
Dimmable: Yes

DESIGN AND FINISHING

Color: Black
Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
LED lamp(s) included: No
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 7 SDCM
Color rendering index (CRI): ≥ 80
Color temperature: 2700-5000 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 88
lm/W

MISCELLANEOUS

Especially designed for: Garden
Balcony

OTHER CHARACTERISTICS

Lamp current: 300 mA

POWER CONSUMPTION

Voltage: 12 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1 kg
Overall height: 518 mm
Overall length: 108.5 mm
Overall width: 108.5 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Lumen output bulb included: 400
Diameter: 108.5 mm
Total lumen output fixture: 320
Light color: Coloured and white light (RGBW)
Wattage bulb included: 3.6
Maximum wattage replacement bulb: 3.6
IP code: UL03 | Wet Location
Class of protection: UL non-earthed
Light source replaceable: No
Number of light sources: 1

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604646
Net weight: 1 kg
Gross weight: 1.26 kg
Height: 15.3 cm
Length: 14 cm
Width: 55.9 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.