

Outdoor LED Strip 16.4ft

Create a magical, exciting, or relaxing ambiance for all your outdoor spaces with the bendable, weatherproof WiZ outdoor LED strip light. Transform your garden, walkway, driveway, porch, terrace, or balcony with uniform lines of vibrant color or shades of white light from cool to cozy. Outdoor LED strip lights participate in the same WiZ ecosystem you already love for your indoor and outdoor WiZ lights. Which means they're easy to install and control using the WiZ app, WiZmote, or your voice over your existing home Wi-Fi. These bendable LED strips will work alone or together with your other outdoor WiZ lights to make your great outdoors more beautiful and inviting than ever before.

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- IP65 (Adaptor IP44)/Plastic




Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



Waterproof and weatherproof

This light is designed for you to enjoy the outdoors as it is waterproof and weather proof. Made with materials that are UV resistant, as well as resistant to wind and snow. Passed rigorous tests to ensure it withstands most weather conditions.



Low-voltage technology and easy installation

Designed for outdoor enjoyment! No complicated wiring or special installation required—just plug it in and go. If you want to change the light's location, just unscrew the adapter and move it somewhere else.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Outdoor
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: Yes
Power adapter included: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 7 SDCM
Color rendering index (CRI): ≥80
Color temperature: 2700-5000 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 26
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Entertainment room Bedroom
Children's room

OTHER CHARACTERISTICS

Lamp current: 410 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 100-120 V
Power: 24

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.57 kg
Overall height: 54.5 mm
Overall length: 7,940 mm
Overall width: 52 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 630
Light color: Coloured and white light (RGBW)
Wattage bulb included: 24
IP code: IP65 (Adaptor IP44)
Class of protection: UL non-earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604738
Net weight: 1.55 kg
Gross weight: 1.75 kg
Height: 7.8 cm
Length: 35.8 cm
Width: 35.8 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.