



Spot 50W PAR16 GU10 x3



The WiZ LED GU10 full color spot beam bulb brings smart lighting for your daily living. Ideal for accent, display and task lighting. Create the ambience of your choice with 16 million colors as well as warm to cool white light. You can set schedules to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Full color smart bulb
- Up to 400 lumens
- Easy plug and play
- Control with app or voice



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



Light that fits in any standard fixture

Compact shape that fits perfectly into any spot and recessed light fixture.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: PAR16
Socket: GU10
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.055 kg

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

LIGHT CHARACTERISTICS

Beam angle: 40 degree(s)
Color consistency: 4 SDCM
Color rendering index (CRI): ≥90
Color temperature: 2200-6500 K
Light Color Category: Full color
Nominal luminous flux: 400 lm
Starting time: <1 s
Warm-up time to 60% light: instant
full light
Luminous Efficacy (rated) (Nom): 81
lm/W

OTHER CHARACTERISTICS

Lamp current: 50 mA

PACKAGING INFORMATION

EAN: 046677605230
EOC: 605238
Product title: 4.9GU10/Wi-Fi BLE
Color/922-65 4/3CT

POWER CONSUMPTION

Power factor: 0.7
Voltage: 120 V
Wattage equivalent: 50 W
Power: 4.9 W

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 58 mm
Overall length: 58 mm
Overall width: 50 mm

RATED VALUES

Rated lifetime: 25,000
Rated luminous flux: 400 lm
Rated peak intensity: 502 cd
Rated power: 4.9 W

TECHNICAL SPECIFICATIONS

Frequency: 60

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Google Home IFTTT
Klikaanklikuit Matter Samsung
Smarthings Sonos

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677605230
Net weight: 0.17 kg
Gross weight: 0.27 kg
Height: 17.4 cm
Length: 7.1 cm
Width: 18.5 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.