



Fairy Light 65.6ft

Fun , fantastic, full-color WiZ fairy lights bring the magic to all your holidays, parties, intimate get-togethers, and daily vibes. Wrap these strings of 160 LEDs around your Christmas tree, your front door on Halloween, your game room on Saturday night, your garden for dining outdoors on those warm summer evenings, or around your bedroom or dining room any day of the week. Static and dynamic light modes dazzle with over 16 million available colors and 8 different zones so that you can DIY your light to your heart's content. And because it's WiZ, you can control your lights' magical sparkling color from anywhere using the WiZ app. You can even sync your fairy lights to music for extra fun and festivity...

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- UL03 - Wet Location (North America)/Plastic



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Control your smart lights from anywhere

No need to worry if lights were left on while no one's home. Simply turn them off from wherever you are, with your smartphone.



Sync Lights to Music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronize your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.



Millions of colors on a single cable

Each fairy light cable lets you choose from millions of colors to create amazing atmospheres that bring the magic and lift your mood.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Color: Black
Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes
LED integrated: Yes
On/off switch on wire: No
Power adapter included: Yes
Remote control included: No
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color rendering index (CRI): -
Color temperature: 2700-5000 K
Warm-up time to 60% light: 2

STRING LIGHT/LIGHTSTRIP

Extendibility: No

MISCELLANEOUS

Especially designed for: Balcony
Bedroom Living Room Garden

OTHER CHARACTERISTICS

Lamp current: 260 mA

POWER CONSUMPTION

Voltage: 100-120 V
Power: 13

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.567 kg
Overall length: 20,000 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA
Bulb technology: LED
Light color: Gradient coloured light (RGBIC)
Wattage bulb included: 15
Class of protection: UL non-earthed
UL Wet/ damp/ dry location: Wet location

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems: Alexa Enki Google Home Homey IFTTT Matter Samsung Smartthings Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677605506
Net weight: 0.57 kg
Gross weight: 0.82 kg
Height: 8.7 cm
Length: 22.4 cm
Width: 22.4 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.