



# LED Strip RGBIC 65.6ft

Our 20 m RGBIC light strips are designed to fit and beautify medium-sized spaces with over 16 million solid colors. Go beyond solid colors with individually controllable full-color segments for dazzling effects like chasing rainbows, color fades, and sparkles. Stick the flexible strip anywhere you like and use the intuitive WiZ app to control your lights using your existing Wi-Fi. Static and dynamic light modes, smart dimming, and light scheduling put you in charge of your whole system—even when you're away from home. Works with Google Home, Amazon Alexa, and Apple HomeKit for the ultimate in ease of use.

## **PRODUCT HIGHLIGHTS**

- Full color
- IP20/Plastic

EAN: 046677605599 wizconnected.com





#### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



## Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



## Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



#### Sync Lights to Music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronize your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.



#### Starter kit easy to cut and extend

2 meter / 6.6 feet starter kit. Cut it or extend it easily to the length that best fits your idea. Extendable up to 10 meters (extension sold separately).



## Static and dynamic light modes to lift your mood

Choose from millions of colors or from the set of light modes we've designed for you. With so many options, you can bring the magic to all your holidays, parties, intimate get-togethers, and daily vibes!

EAN: 046677605599 wizconnected.com



# **SPECIFICATIONS**

#### **BULB CHARACTERISTICS**

Intended use: Indoor Dimmable: Yes

#### **DESIGN AND FINISHING**

Color: White Material: Plastic

#### **DURABILITY**

Average life (at 2.7 hrs/day): 15 year(s) Lumen maintenance factor: 70% Number of switch cycles: 50,000 Nominal lifetime: 15,000

#### EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes LED integrated: Yes On/off switch on wire: Yes Power adapter included: Yes Remote control included: No

#### LIGHT CHARACTERISTICS

Color rendering index (CRI): -Color temperature: NA Warm-up time to 60% light: 2

#### **MISCELLANEOUS**

Especially designed for: Living Room Entertainment room Bedroom Children's room

#### **OTHER CHARACTERISTICS**

Lamp current: 560 mA

#### **POWER CONSUMPTION**

Power factor: 0.5 Voltage: 100-240 V Power Consumption: 30.6

#### PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.43 kg Overall height: 2.1 mm Overall length: 20,000 mm Overall width: 10 mm

#### **SERVICE**

Warranty: 2 year(s)

## **TECHNICAL SPECIFICATIONS**Total lumen output fixture: -

Light color: RGB Wattage bulb included: 36 IP code: IP20 | Finger-protected Class of protection: Class II - Double Insulated

#### **WHAT'S SUPPORTED**

Compatible with Effects: Yes

WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

#### PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677605599 Net weight: 0.65 kg Gross weight: 0.85 kg Height: 18.7 cm

Length: 8.2 cm Width: 18.9 cm

### **Signify**

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: 046677605599 wizconnected.com