

PHILIPS

Blaise Wall Lights
1.5W

UltraEfficient Solar

3000K

Anthracite

Linkable; Sensor; Solar; Water
Resistant



046677607241



Long-lasting solar-powered garden light for all seasons

Philips has developed an UltraEfficient solar LED outdoor light that uses new technology to cut carbon emissions, reduce material waste, and lower energy usage. With an amazing 50,000 hour lifetime it lasts more than 5 times longer than the Philips LED outdoor light equivalents. Just what is needed for a more sustainable planet.

Easy installation

- No wiring required

Sustainable light solutions

- Long lifetime up to 50,000 hours

Premium quality

- Durable design with PowerShield coating

Designed for outdoors

- IP44 - weather proof

Special characteristics

- Dual-brightness light

046677607241

High quality light

- Bright white light 3000K

Highlights

No wiring required



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while having the perfect light ambiance in your home.

Durable design



Protected by PowerShield To keep your outdoor lights in excellent condition, we use a high-performance powder coating powered by Interpon, an AkzoNobel brand. Tougher than traditional paints, it protects against fading, scratches, dents, and rust for long-lasting beauty and performance.

IP44 - weather proof




This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Dual-brightness light

Create a flexible and appealing ambiance with the dual-brightness feature. The light dims when idle and automatically brightens when people are present, delivering the right level of light whenever you need it.

Bright white light 3000K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces bright white light at 3000 K.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Color: Anthracite
- Material: Metal, Plastic

Durability

- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centerpiece: No

Light characteristics

- Beam angle: 120
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED Innovations: UltraEfficient
- Extra Features: Linkable, Sensor, Solar, Water Resistant

Power consumption

- Wattage: 1.5 W
- Power: 1.5 W

Product dimensions and weight

- Net weight: 0.5 kg
- Overall height: 140 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Total lumen output fixture: 250/20
- Bulb technology: LED
- Light color: 3000
- Mains power: DC 4
- Energy class included light source: B
- IP code: IP44
- Class of protection: Class III - Safe Extra Low Voltage
- Light source replaceable: No
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677607241
- Net weight: 0.5 kg
- Gross weight: 0.66 kg
- Height: 18.8 cm
- Length: 14.5 cm
- Width: 15.5 cm



Issue date: 2026-05-13
Version: 0.83

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com