

PHILIPS

Filament Bulb Frosted
100W A21 E26

LED

2700/3000/4000/5000/6500
K

1500lm

15000h

Dimming

046677610838



Selectable colour temperatures help you to make the right choice

Enjoy 5 possible light colors in one product. Change the color of your light easily with by switching the button on the product.

High quality light

- Designed for the comfort of your eyes

Create the right light for your home

- Perfect for decorative fixtures

Dimmable (LED Lamps)

- Dimmable (LED Lamps)

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Perfect for decorative fixture



Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips, and post lights.

Dimmable (LED Lamps)



This lamp can be used with most dimmers to create your desired ambience with smooth dimming. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this lamp.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Choose your color: Yes
- LED integrated: Yes

Light characteristics

- Beam angle: 300
- Color rendering index (CRI): 90
- Color temperature: 2700/3000/4000/5000/6500
- Nominal luminous flux: 1500 lm
- Luminous Efficacy (rated) (Nom): 136

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Packaging information

- EAN: 046677610838
- EOC: 610832
- Product title: 11A21/Dip/5CCT/FR/G/E26/DIM/T20 1PK

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 100
- Power: 11

Product dimensions and weight

- Overall height: 140 mm
- Overall length: 140 mm
- Overall width: 70 mm

Technical specifications

- Frequency: 60
- Diameter: 70 mm
- Bulb technology: LED
- can it be used in closed luminaires:
No

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems:
Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677610838
- Net weight: 0.07 kg
- Gross weight: 0.12 kg
- Height: 18.1 cm
- Length: 8.1 cm
- Width: 7.6 cm

