









































106/300 6KV 10KV

At  $90^{\circ}\,0,26m^{2}$  At  $0^{\circ}\,0,04m^{2}$  At  $15^{\circ}\,0,10m^{2}$ 

RG1

Inrush Current (230VAC) (Apk/μs)
Luminaire Surge Protection
Luminaire Surge Protection with SPD Optional

Tour of all adviced county at the standard	U-4:	Maximun number of luminaires to install				
Type of electrical protection insta	liation	1 driver 150W	2 driver 150W			
NACD1CA	ВТҮРЕ	8	4			
MCB16A	СТҮРЕ	13	6			
MCB10A	ВТҮРЕ	4	2			
MCBTOA	СТҮРЕ	8	4			



Tc max. of PCBA = 95°C Measurement in LED nr 63.

led color	ledgine	LEDs	Lamp lumen +/- 7%	<b>W</b> +/- 11%	<b>(</b>		∦ Ta Max. 8°C	∦ Ta Max. ℃	∦ Ta Min. 8 °C	kg standard	citytouch
	LED70-4S	- 48	7200	44	-		45	35	-40	15 Kg	16Kg
	LED80-4S		8000	49							
	LED100-4S	64	10000	60							
	LED120-4S	04	12000	73							
	LED140-4S		14000	87						16Kg	17kg
	LED160-4S		16000	100							
	LED180-4S	82	18000	112							
	LED200-4S	-	20000	128		<b>✓</b>					
740/	LED220-4S		22000	142							
757	LED240-4S		24000	148							
	LED260-4S	- - 120 -	26000	160							
	LED280-4S		28000	176							
	LED300-4S		30000	190							
	LED320-4S		32000	205							
	LED340-4S		34000	220							
	LED360-4S		36000	235			45*	35*			
	LED380-4S		38000	255				رر			
	LED400-4S		40000	270			35	25			


led color	ledgine	LEDs	Lamp lumen +/- 7%	<b>W</b> +/- 11%	(1)		∦ Ta Max. °C	∦ Ta Max. °C	∦ Ta Min. °C	kg	citytouch
	15070.46		7000				Outdoor	Indoor		Standard	citytoden
	LED70-4S	48	7000	56						15 Kg	16Kg
	LED90-4S		9000	76							
	LED110-4S	64	11000	90	_				_		
	LED130-4S LED140-4S		13000	106	-	<b>~</b>	45	35	-40	16Kg	17kg
		- - 82 -	14000	116							
LED160-4	LED160-4S		16000	136							
	LED180-4S		18000	158							
830	LED200-4S		20000	164							
	LED220-4S	-	22000	184							
	LED240-4S		24000	205							
LED260-4S LED280-4S	120	26000	225	•							
	LED280-4S	120	28000	245	- - -				_		
	LED300-4S	-	30000	270			35	25			
	LED320-4S		32000	295							
	LED340-4S		34000	320			25	15			





This luminaire must be installed only by qualified personnel





Disconnect before servicing















## CITYTOUCH BOX INSTALLATION / FIXATION











## TYPES OF MAIN CONNECTOR



































## CITYTOUCH CONNECTION Ø10-14 mm 2-4 mm<sup>2</sup>





Click!







© 2016 Philips Lighting Holding B.V. All rights reserved Reproduction in whole or in part is prohibited without consent of the copyright owner The information presented in this document does not form part of any quotation or contract is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights

Philips Lighting Holding B.V. The Netherlands