







PHILIPS

CoreLine Panel

RC133V




|                                          | Lumen(lm)       | CCT(K)          | P(W)      | IP        | IK   | L×W×H1/H2(mm) | kg   |
|------------------------------------------|-----------------|-----------------|-----------|-----------|------|---------------|------|
| RC133V G6 36S/840 PSU W62L62 NOC         | 3600            | 4000            | 26.00     | IP40/IP20 | IK02 | 620x620x34/59 | 1.80 |
| RC133V G6 36S/840 PSU W62L62 OC          | 3600            | 4000            | 26.00     | IP40/IP20 | IK02 | 620x620x35/60 | 2.20 |
| RC133V G6 36S/840 PSD W62L62 OC          | 3600            | 4000            | 26.00     | IP40/IP20 | IK02 | 620x620x35/60 | 2.00 |
| RC133V G6 29_36_43S/830_40 PSU W62L62 OC | 2900/*3600/4300 | 3000/3500/*4000 | 22/*26/31 | IP40/IP20 | IK02 | 620x620x35/60 | 2.10 |
| RC133V G6 29_36_43S/830_40 PSD W62L62 OC | 2900/*3600/4300 | 3000/3500/*4000 | 22/*26/31 | IP40/IP20 | IK02 | 620x620x35/60 | 2.10 |
| RC133V G6 36S/840 WIA W62L62 OC          | 3600            | 4000            | 26.00     | IP40/IP20 | IK02 | 620x620x35/70 | 2.15 |
| * Default setting                        |                 |                 |           |           |      |               |      |




Available as accessory (Need to purchase separately)


**Suspension set:**  
911401809387  
RC159Z Suspension set SME-4 WH  
911401809487  
RC159Z Suspension set SME-3 WH




**Surface mounted set:**  
911401807887  
RC159Z SMB W62L62



**Plaster ceiling set:**  
911401809287  
RC159Z Plaster Ceiling  
SMB-PLC





**Safety cable:**  
911401809187  
RC159Z Safety Cable






## Quick-connectors




## VPC Visible Profile Ceiling/ Lay-In mounting

Optional with  
911401809187 RC159Z Safety Cable




## Safety cable



## PCV plaster ceiling version (IK02)


Optional with  
911401809287 RC159Z Plaster Ceiling SMB-PLC





## Surface mounted

Optional with  
911401807887:RC159Z SMB W62L62




## Suspension


Optional with  
911401809387 RC159Z Suspension set SME-4 WH  
911401809487 RC159Z Suspension set SME-3 WH

### PSU/ WIA

911401809487  
RC159Z Suspension set SME-3 WH




1a




### PSD



911401809387  
RC159Z Suspension set SME-4 WH




1b




### PSD Touch & Dim





2




3





|                  |                  |        |             |         |       |
|------------------|------------------|--------|-------------|---------|-------|
| 830/840<br>CRI80 | Lumen selectable | 3000K  | 3500K/4000K | Wattage | Iout  |
|                  | High             | 4000lm | 4300lm      | 31W     | 650mA |
|                  | Middle           | 3400lm | 3600lm      | 26W     | 550mA |
|                  | Low              | 2900lm | 3100lm      | 22W     | 480mA |

## Inrush current



|                            | PSU                    |     | PSD  |     | WIA |
|----------------------------|------------------------|-----|------|-----|-----|
|                            | 26W                    | 31W | 26W  | 31W | 31W |
| Electrical characteristics |                        |     |      |     |     |
| I <sub>max</sub> (A)       | 16                     | 20  | 25.2 | 26  | 4.8 |
| T <sub>ref</sub> (us)      | 200                    | 220 | 260  | 260 | 56  |
| MCB                        | No. of luminaires max. |     |      |     |     |
| B-10 A                     | 18                     | 13  | 9    | 8   | 32  |
| B-16A                      | 30                     | 21  | 17   | 15  | 50  |
| C-10 A                     | 32                     | 23  | 17   | 15  | 52  |
| C-16A                      | 51                     | 37  | 29   | 28  | 85  |