


1 x TLED 26.7W 6500K 9290037752

1 x 3900 lm

Polar intensity diagram




Light output ratio 1.00
 Service upward 0.24
 Service downward 0.76

CIE flux code 36 64 85 76 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.40	0.38	0.38	0.38	0.37	0.29	0.27	0.23	0.25	0.21	0.18	0.18
0.80	0.50	0.47	0.48	0.46	0.45	0.37	0.34	0.29	0.32	0.27	0.23	0.23
1.00	0.58	0.54	0.55	0.53	0.51	0.44	0.40	0.35	0.37	0.33	0.28	0.28
1.25	0.66	0.60	0.62	0.60	0.58	0.50	0.46	0.41	0.43	0.38	0.33	0.33
1.50	0.72	0.65	0.68	0.65	0.62	0.55	0.51	0.46	0.47	0.43	0.37	0.37
2.00	0.81	0.73	0.77	0.73	0.69	0.63	0.58	0.54	0.54	0.50	0.43	0.43
2.50	0.88	0.77	0.83	0.78	0.74	0.68	0.63	0.59	0.58	0.55	0.48	0.48
3.00	0.92	0.81	0.87	0.82	0.78	0.72	0.67	0.63	0.62	0.59	0.51	0.51
4.00	0.99	0.86	0.93	0.87	0.82	0.78	0.72	0.69	0.66	0.64	0.55	0.55
5.00	1.03	0.88	0.97	0.91	0.85	0.81	0.75	0.72	0.69	0.67	0.58	0.58

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	25028	24847	25530	26370	28262	32418	39209
50.0	24093	23844	24496	25184	26966	31174	38520
55.0	23397	23027	23595	24038	25583	29702	37471
60.0	22692	22249	22781	22988	24295	28137	36105
65.0	22115	21618	22141	22049	23023	26405	34324
70.0	21748	21135	21588	21213	21867	24526	31907
75.0	21403	20714	21149	20511	20863	22453	28347
80.0	21203	20484	20967	20045	20061	20245	22896
85.0	21279	20463	20946	19876	19780	18586	14874
90.0	21481	20594	21137	20031	20056	18980	3047

(cd/m²)

s23120014a

2024-01-31