



PHILIPS

Maxos universal

Special through wire
T7 5ft, T9 5ft



50Hz
60Hz

220V
240V



LEDs

IP20



GLOW
WIRE
650°C

Max.
35°C
Min.
-20°C





Length
(mm)



910925869522	LL515Z WIRING 5x1.5 UNIV WH
910925869523	LL515Z WIRING 7x1.5 UNIV WH

1600
1600

0.5
0.5



	LED42S	LED46/57S	LED80S
	Xitanium 35W 0.08-0.35A	Xitanium 50W 0.2-0.25A	Xitanium 90W 0.15-0.5A
Driver Type	220V TD21 230V	100-200V DS 230V	300V TD21 230V
I _{max} (A)	23.1	20.2	25
T _{ref} (μs)	221	278	230
MCB			
B 10A	13	24	12
B 13A	17	33	16
B 16A	22	41	20
C 10A	22	41	20
C 13A	29	55	27
C 16A	37	69	34



583 - 442710478800


2023-06-21
© Signify Holding
All rights reserved

Printed in EU
Data subject to change without notice
Keep for future reference: www.philips.com/lighting



LL515S / LL515S PCO


With Spring A or B (pre-installed)



LL515S Blind Unit

(with spring A or B, not included in box)

910925869521 LL515Z BC UNIV WH




1



Scan me!



2



Register me!

SCAN



To get an overview of all spare parts for a luminaire, please refer to detailed instructions in the service manual available via the Signify Service tag apps (Android and iOS).





© 2023 Signify Holding

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding
The Netherlands