


DN020B G4 LED6 7W D100 1 x 9290032787 4000K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
Service upward 0.00
Service downward 1.00


CIE flux code 50 80 96 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80				0.70				0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.50	0.48	0.49	0.48	0.47	0.40	0.40	0.35	0.39	0.35	0.33	0.33
0.80	0.61	0.57	0.60	0.58	0.56	0.49	0.48	0.44	0.48	0.43	0.41	0.41
1.00	0.70	0.65	0.68	0.66	0.64	0.57	0.56	0.51	0.55	0.51	0.48	0.48
1.25	0.78	0.71	0.76	0.73	0.71	0.64	0.63	0.58	0.62	0.58	0.56	0.56
1.50	0.84	0.77	0.82	0.79	0.76	0.69	0.68	0.64	0.67	0.63	0.61	0.61
2.00	0.94	0.84	0.92	0.87	0.83	0.78	0.77	0.73	0.75	0.72	0.69	0.69
2.50	1.01	0.89	0.98	0.93	0.88	0.83	0.82	0.78	0.80	0.78	0.75	0.75
3.00	1.05	0.92	1.02	0.96	0.91	0.87	0.86	0.83	0.84	0.82	0.79	0.79
4.00	1.11	0.96	1.08	1.01	0.95	0.92	0.90	0.88	0.89	0.87	0.84	0.84
5.00	1.15	0.99	1.11	1.04	0.98	0.95	0.93	0.91	0.91	0.90	0.87	0.87

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18360	18360	18360	18360	18360	18360	18360
50.0	17647	17647	17647	17647	17647	17647	17647
55.0	16920	16920	16920	16920	16920	16920	16920
60.0	16169	16169	16169	16169	16169	16169	16169
65.0	15380	15380	15380	15380	15380	15380	15380
70.0	14533	14533	14533	14533	14533	14533	14533
75.0	13588	13588	13588	13588	13588	13588	13588
80.0	12432	12432	12432	12432	12432	12432	12432
85.0	10648	10648	10648	10648	10648	10648	10648
90.0	9308	9308	9308	9308	9308	9308	9308

(cd/m²)

2023-05-18