



DN020B G4 LED6 6W D125 1 x 9290032789 3000K**1 x 550 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 79 95 100 100

UGRcen (4Hx8H, 0.25H) 25

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80			0.70			0.50			0.30		
	0.50			0.50			0.30			0.10		
0.60	0.50	0.47	0.49	0.48	0.47	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	0.40
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	0.60
2.00	0.93	0.83	0.91	0.87	0.82	0.77	0.76	0.72	0.74	0.71	0.69	0.69
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.90	0.86	0.85	0.82	0.83	0.81	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	11396	11396	11396	11396	11396	11396	11396
50.0	10999	10999	10999	10999	10999	10999	10999
55.0	10590	10590	10590	10590	10590	10590	10590
60.0	10160	10160	10160	10160	10160	10160	10160
65.0	9706	9706	9706	9706	9706	9706	9706
70.0	9213	9213	9213	9213	9213	9213	9213
75.0	8663	8663	8663	8663	8663	8663	8663
80.0	8020	8020	8020	8020	8020	8020	8020
85.0	7063	7063	7063	7063	7063	7063	7063
90.0	10862	10862	10862	10862	10862	10862	10862

(cd/m²)

2023-05-18