


DN020B G4 LED9 10.5W D125 1 x 9290032793 4000K


1 x 900 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 79 95 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80			0.70			0.50			0.30		
	0.50			0.50			0.30			0.10		
0.60	0.50	0.47	0.49	0.48	0.47	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	0.40
1.00	0.69	0.64	0.67	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.57	0.61	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.66	0.62	0.60	0.60
2.00	0.93	0.83	0.91	0.87	0.82	0.77	0.76	0.72	0.74	0.71	0.69	0.69
2.50	1.00	0.88	0.97	0.92	0.87	0.82	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.90	0.86	0.85	0.82	0.83	0.81	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18614	18614	18614	18614	18614	18614	18614
50.0	17954	17954	17954	17954	17954	17954	17954
55.0	17273	17273	17273	17273	17273	17273	17273
60.0	16577	16577	16577	16577	16577	16577	16577
65.0	15836	15836	15836	15836	15836	15836	15836
70.0	15064	15064	15064	15064	15064	15064	15064
75.0	14207	14207	14207	14207	14207	14207	14207
80.0	13213	13213	13213	13213	13213	13213	13213
85.0	11640	11640	11640	11640	11640	11640	11640
90.0	23739	23739	23739	23739	23739	23739	23739

(cd/m²)

2023-05-18