


DN200 G3 LED12 1 x 9290032716 3000K


1 x 1150 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 46 77 94 100 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10	0.80	0.50	0.30	0.10
0.60	0.48	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.63	0.61	0.54	0.53	0.48	0.52	0.48	0.45	0.45
1.25	0.76	0.69	0.74	0.71	0.68	0.61	0.60	0.55	0.59	0.55	0.53	0.53
1.50	0.82	0.74	0.80	0.77	0.73	0.67	0.66	0.61	0.65	0.60	0.58	0.58
2.00	0.92	0.82	0.90	0.85	0.81	0.75	0.74	0.70	0.73	0.69	0.67	0.67
2.50	0.99	0.87	0.96	0.91	0.86	0.81	0.80	0.76	0.78	0.75	0.72	0.72
3.00	1.03	0.91	1.00	0.95	0.89	0.85	0.83	0.80	0.82	0.79	0.76	0.76
4.00	1.09	0.95	1.06	0.99	0.94	0.90	0.88	0.86	0.87	0.84	0.82	0.82
5.00	1.13	0.97	1.10	1.02	0.96	0.93	0.91	0.89	0.90	0.88	0.85	0.85

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23691	23691	23691	23691	23691	23691	23691
50.0	23316	23316	23316	23316	23316	23316	23316
55.0	22912	22912	22912	22912	22912	22912	22912
60.0	22471	22471	22471	22471	22471	22471	22471
65.0	21989	21989	21989	21989	21989	21989	21989
70.0	21459	21459	21459	21459	21459	21459	21459
75.0	20852	20852	20852	20852	20852	20852	20852
80.0	20132	20132	20132	20132	20132	20132	20132
85.0	18929	18929	18929	18929	18929	18929	18929
90.0	48012	48012	48012	48012	48012	48012	48012

(cd/m²)

2023-01-05