


DN200 G3 LED15 1 x 9290032721 6500K

1 x 1500 lm

Polar intensity diagram




Light output ratio 1.00
Service upward 0.00
Service downward 1.00

CIE flux code 46 77 95 100 100

UGRcen (4Hx8H, 0.25H) 29

Quantity estimation diagram




Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70 0.70 0.70				0.50 0.50 0.30 0.30			
	0.80	0.80	0.50	0.50	0.70	0.70	0.70	0.70	0.50	0.50	0.30	0.30
0.60	0.48	0.45	0.47	0.46	0.45	0.37	0.37	0.32	0.36	0.32	0.30	0.30
0.80	0.58	0.55	0.57	0.56	0.54	0.46	0.46	0.41	0.45	0.40	0.38	0.38
1.00	0.67	0.62	0.66	0.63	0.61	0.54	0.53	0.48	0.52	0.48	0.45	0.45
1.25	0.76	0.69	0.74	0.71	0.68	0.61	0.60	0.55	0.59	0.55	0.53	0.53
1.50	0.82	0.75	0.80	0.77	0.74	0.67	0.66	0.61	0.65	0.61	0.58	0.58
2.00	0.92	0.82	0.90	0.85	0.81	0.76	0.74	0.70	0.73	0.69	0.67	0.67
2.50	0.99	0.87	0.96	0.91	0.86	0.81	0.80	0.76	0.79	0.75	0.73	0.73
3.00	1.04	0.91	1.01	0.95	0.90	0.85	0.84	0.81	0.82	0.80	0.77	0.77
4.00	1.10	0.95	1.07	1.00	0.94	0.91	0.89	0.86	0.87	0.85	0.82	0.82
5.00	1.14	0.98	1.10	1.03	0.97	0.94	0.92	0.90	0.90	0.88	0.86	0.86

Ceiling mounted

UGR diagram



Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	27792	27792	27792	27792	27792	27792	27792
50.0	27315	27315	27315	27315	27315	27315	27315
55.0	26789	26789	26789	26789	26789	26789	26789
60.0	26217	26217	26217	26217	26217	26217	26217
65.0	25580	25580	25580	25580	25580	25580	25580
70.0	24871	24871	24871	24871	24871	24871	24871
75.0	24017	24017	24017	24017	24017	24017	24017
80.0	22910	22910	22910	22910	22910	22910	22910
85.0	20761	20761	20761	20761	20761	20761	20761
90.0	33463	33463	33463	33463	33463	33463	33463

(cd/m²)

2023-01-05