




DN020 G3 LED6 CW 7W 220-240V D 1 x 9290025093 6500K

1 x 600 lm

Polar intensity diagram**Quantity estimation diagram****UGR diagram**

Light output ratio 1.02
Service upward 0.01
Service downward 1.01

CIE flux code 46 78 95 99 102

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)														
	0.80 0.80			0.70 0.70 0.70 0.70				0.50 0.50			0.30 0.30			0.00	
	0.50 0.50	0.30 0.10	0.30 0.10	0.50 0.50	0.30 0.20	0.10 0.10	0.10 0.10	0.30 0.10	0.10 0.10	0.10 0.10	0.30 0.10	0.10 0.10	0.10 0.10	0.00	0.00
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.37	0.32	0.30	0.30	0.30
0.80	0.59	0.56	0.58	0.56	0.55	0.47	0.46	0.41	0.46	0.41	0.46	0.41	0.39	0.39	0.39
1.00	0.68	0.63	0.67	0.65	0.63	0.55	0.54	0.49	0.53	0.48	0.53	0.48	0.46	0.46	0.46
1.25	0.77	0.71	0.75	0.72	0.70	0.63	0.61	0.56	0.60	0.56	0.60	0.56	0.53	0.53	0.53
1.50	0.84	0.76	0.82	0.78	0.75	0.68	0.67	0.62	0.66	0.62	0.66	0.62	0.59	0.59	0.59
2.00	0.94	0.84	0.92	0.87	0.83	0.77	0.76	0.71	0.74	0.71	0.74	0.71	0.68	0.68	0.68
2.50	1.01	0.89	0.98	0.93	0.88	0.83	0.81	0.78	0.80	0.76	0.80	0.76	0.74	0.74	0.74
3.00	1.06	0.93	1.03	0.97	0.91	0.87	0.85	0.82	0.84	0.81	0.84	0.81	0.78	0.78	0.78
4.00	1.12	0.97	1.08	1.02	0.96	0.92	0.90	0.87	0.88	0.86	0.88	0.86	0.83	0.83	0.83
5.00	1.16	0.99	1.12	1.05	0.98	0.95	0.93	0.91	0.91	0.89	0.91	0.89	0.86	0.86	0.86

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23911	23911	23911	23911	23911	23911	23911
50.0	23445	23445	23445	23445	23445	23445	23445
55.0	22999	22999	22999	22999	22999	22999	22999
60.0	22315	22315	22315	22315	22315	22315	22315
65.0	21626	21626	21626	21626	21626	21626	21626
70.0	20753	20753	20753	20753	20753	20753	20753
75.0	19396	19396	19396	19396	19396	19396	19396
80.0	17819	17819	17819	17819	17819	17819	17819
85.0	14807	14807	14807	14807	14807	14807	14807
90.0	2333	2333	2333	2333	2333	2333	2333

(cd/m²)

2020-08-24