

Parterre Post Light

7.5W

myGarden

Parterre

black

LED



16482/30/PO



## Enjoy a beautiful garden with light

The Philips Parterre LED black outdoor post light suspends a cube of light within a durable die-cast aluminium cradle. The ingenious design casts beams of diffused warm white light over pathways and open areas outdoors.

### Sustainable light solutions

- High quality LED light

### Designed for outdoors

- High-quality aluminium and superior synthetics

### Special characteristics

- Weather-proof

# Highlights

## High quality LED light

The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

## Weather-proof



two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Metal

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: Yes

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Post Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Power consumption

- Power: 7.5

## Product dimensions and weight

- Net weight: 1.855 kg
- Overall height: 770 mm
- Overall length: 100 mm
- Overall width: 100 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 800 lm
- Mains power: 50 Hz
- Energy class included light source: F
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No
- Number of light sources: 1

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696158869
- Net weight: 1.86 kg
- Gross weight: 2.06 kg
- Height: 82.5 cm
- Length: 11 cm
- Width: 11 cm



Issue date: 2026-01-31  
Version: 0.532

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)