

PHILIPS

Stratosphere Wall Light 9W

myGarden

4000K

Antracite

Water Resistant



16487/93/P3



Enjoy a beautiful garden with light

The Philips Stratosphere LED outdoor wall light in anthracite grey is made from durable die-cast aluminium. The design provides bi-directional light distribution to illuminate your wall with plenty of diffuse bright light.

Sustainable light solutions

- Energy saving
- High quality LED light

Bring design into your garden

- High-quality aluminium and superior synthetics

Advanced light for outdoors

- Compatible with in-wall dimmers
- Philips offers a 5-year warranty on the LED module and driver

Special characteristics

- Easy installation
- Weather-proof
- Long operating life of up to 30 years

Highlights

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light

The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

Compatible with in-wall dimmers



Adjust the brightness of this Philips light with an in-wall dimmer (not included) to set the mood in the room, highlight a feature of your home and more.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Easy installation



Installing a luminaire can be sometimes difficult, with this Philips outdoor lamp, you can be sure that high attention has been given to facilitate it and simplify it for you. This article is delivered with a torx key to used during installation.

Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

Long operating (30 yrs)



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 30,000 hours (which equals 30 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Aluminium

Durability

- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: Yes
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.529 kg
- Height: 7.6 cm
- Length: 20.3 cm
- Width: 9.3 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Light source equivalent to traditional bulb of: 44 W
- Total lumen output fixture: 1000 lm
- Bulb technology: LED
- Light colour: cool white
- Mains power: 50-60 Hz
- Energy class included light source: F
- Wattage bulb included: 4.5 W
- IP code: IP44
- Class of protection: Class I
- Light source replaceable: No
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC – product: 8718696161395
- Net weight: 0.53 kg
- Gross weight: 0.61 kg
- Height: 11.1 cm
- Length: 8.6 cm
- Width: 21.1 cm



Issue date: 2025-06-12
Version: 0.554

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com