

PHILIPS

Fresco Recessed
light 4.6W

myGarden

2700K

Inox

Water Resistant



17289/47/16



Illuminate your garden at night

The Philips myGarden Fresco recessed spot has beautiful LED light to show garden features at their best, or illuminate dark areas clearly. It is constructed from durable metal, while the adjustable head allows for a directional beam.

Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life of up to 10 years
- Warm white light

Designed for your garden

- IP23 - weather proof

Highlights

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Long operating life



A light source you can trust. The LED lamp delivered with this Philips LED lamp will last up to 10,000 hours (which equals 10 years on the basis of an average use of 3 hours/day with at least of 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light lamp replacement while having the perfect light ambience in your home.

Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

IP23 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP23: it is protected against spraying water and ideal for lighting a veranda or a porch.

Specifications

Design and finishing

- Colour: Inox
- Material: Metal

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Defined light beams: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.160 kg
- Recessed distance: 110 mm
- Overall height: 108 mm
- Overall length: 100 mm
- Overall width: 100 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture (hidden): 395
- Lumen output bulb included: 395
- Light source equivalent to traditional bulb of: 50
- Bulb technology: LED
- Light colour: warm white
- Mains power: 50-60 Hz
- Energy class included light source: F
- Fitting/cap: GU10
- Wattage bulb included: 5 W
- Maximum wattage replacement bulb: 5
- IP code: IP20
- Class of protection: Class II – Double Insulated
- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8718291502876
- Net weight: 0.16 kg
- Gross weight: 0.24 kg
- Height: 10.8 cm
- Length: 9.3 cm
- Width: 10.3 cm



Issue date: 2025-08-30
Version: 0.445

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com