

# PHILIPS

Antelope Wall Light  
6W

myGarden


4000K

Black

Water Resistant



17320/30/P3



## Enjoy a beautiful garden with light

Philips Antelope LED outdoor wall light in black is fashioned from durable high quality synthetics. The familiar pillbox design casts plenty of diffuse cool white light in all directions for clear illumination of outdoor areas.

### Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life of up to 25 years
- Cool white light
- Philips offers a 5-year warranty on the LED module and driver

### Designed for your garden

- IP44 - weatherproof



# Highlights

## Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## High quality LED light




The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## Long operating life



A light source you can trust. The LED bulb, delivered with this Philips LED lamp, will last up to 25,000 hours (which equals 25 years on the basis of an average use of 3 hours/day with at least of 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

## Cool white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips light offers cool white light that keeps you energised.

## 5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

## IP44 - weatherproof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Plastic

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: Yes

## Garden area

- Garden area: Garden and Patio

## Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 4000 K
- Luminous efficacy (rated) (nom.): 102

## Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Power consumption

- Power: 6

## Product dimensions and weight

- Net weight: 0.45 kg
- Overall height: 269 mm
- Overall length: 199 mm
- Overall width: 89 mm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Total lumen output fixture: 600
- Light colour: Cool white light
- Mains power: 220-240
- Energy class included light source: F
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No
- Number of light sources: 1

## Packaging dimensions and weight

- EAN/UPC - product: 8718696150559
- Net weight: 0.45 kg
- Gross weight: 0.57 kg
- Height: 28.1 cm
- Length: 9.6 cm
- Width: 20.6 cm

