

# PHILIPS

Astilbe Wall Light  
42W E27 No-bulb

myGarden

No bulb

Black

Water Resistant



17380/30/PN



## Enjoy a beautiful garden with light

The Philips Astilbe wall lantern in aluminium adds style and strength to your wall. It distributes the light in 4 directions for a stunning wall-washing effect. All you have to do is enjoy your garden.

### Designed for outdoors

- High-quality aluminium and superior synthetics

### Special characteristics

- Weather-proof

### Enjoy your outdoor life

- Create a stylish and welcoming atmosphere

# Highlights

## High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

## Create a stylish atmosphere

This outdoor wall light is designed around the latest trends and lifestyles to blend effortlessly into your outdoor space and define the ambience you have always desired.

## Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Aluminium

## Extra feature/accessory incl.

- Fully weatherproof: Yes

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 0.505 kg
- Height: 17.5 cm
- Length: 17.8 cm
- Width: 17.8 cm

### Service

- Warranty: 2 year(s)

### Technical specifications

- Mains power: 50-60 Hz
- LED: No
- Energy class included light source: bulb not included
- Fitting/cap: E27
- Wattage bulb included: -
- Maximum wattage replacement bulb: 42 W
- IP code: IP44
- Class of protection: Class II
- Light source replaceable: Yes
- Number of light sources: 1

### Packaging dimensions and weight

- EAN/UPC - product: 8718696165829
- Net weight: 0.51 kg
- Gross weight: 0.65 kg
- Height: 18.9 cm
- Length: 18.1 cm
- Width: 18.1 cm
- Material number (12NC): 915005553201



Issue date: 2024-04-18  
Version: 0.454

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)