

PHILIPS

Actea Wall Light
12W

myGarden

2700K

Black

Water Resistant



17390/30/P0



Enjoy a beautiful garden with light

The Philips Actea LED outdoor wall light in black suspends a round panel of powerful warm white light in an elegant frame of durable die-cast aluminium. A work of luminous art to hang on your wall and illuminate your outdoor space.

Sustainable light solutions

- Energy saving

Bring design into your garden

- High-quality aluminium and superior synthetics

Advanced light for outdoors

- High power LED
- Philips offers a 5-year warranty on the LED module and driver

Special characteristics

- Weather-proof
- Long operating life

Highlights

Energy saving



This Philips light conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and superior synthetics.

High power LED



Philips outdoor lighting uses the latest state-of-the-art LED technology. It offers strong light output, high light quality and a long lifetime.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

Long operating life



Philips LED lights offer an average of up to 20,000 hours (which equals an average of 20 years on basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles).

Specifications

Design and finishing

- Colour: Black
- Material: Metal

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2700 K
- Luminous efficacy (rated) (nom.): 138

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

Power consumption

- Power: 12

Product dimensions and weight

- Net weight: 0.55 kg
- Overall height: 74 mm
- Overall length: 189 mm
- Overall width: 189 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Light source equivalent to traditional bulb of: 83
- Total lumen output fixture: 1200
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: 220-240
- Energy class included light source: F
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718696165928
- Net weight: 0.55 kg
- Gross weight: 0.66 kg
- Height: 20.4 cm
- Length: 8.6 cm
- Width: 19.6 cm



Issue date: 2026-05-13
Version: 0.574

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com