

# PHILIPS

Virginia Motion  
sensor

VIRGINIA

white

17476/31/PN



## Always light when you come home

This white Philips Virginia motion sensor has multiple mounting possibilities, with a wide detection range and free sensor head (two directions). Set the sensor to your needs and use the unique day/night function for safe evenings.

### **Advanced light for outdoors**

- Motion sensor included, for convenience and reassurance
- Manual override

### **Special characteristics**

- Multiple mounting possibilities

### **Feel welcomed home with light**

- Easy-to-set-up sensor
- High max load (1,000 W for incandescent, 200 W for LED)

### **Experience outdoor lighting easily**

- IP44 - weatherproof
- High-quality synthetics

# Highlights

## Motion sensor included



A motion sensor is included to welcome you when you return home or let you know when someone has arrived. When the sensor detects movement, the lamp switches on automatically.

## Manual override Multiple mounting possibilities Easy-to-set-up sensor



A simple set-up procedure makes it easy to select when and for how long the automatic sensor switches on the lamp(s).

## High max load (1,000 W for incandescent, 200 W for LED) IP44 - weatherproof



This Philips PIR sensor is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This Philips PIR sensor is designed with IP44: it is protected against splashing water, ideal for general outdoor use.

## High-quality synthetics

This Philips PIR sensor is made specifically for outdoor spaces. It's hard-wearing and built to last. It's constructed from high-quality synthetics.

# Specifications

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Nominal lifetime: 25,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: No

#### Garden area

- Garden area: Garden and Patio

#### Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Accessories
- EyeComfort: No
- Extra Features: Water Resistant

#### Product dimensions and weight

- Net weight: 0.146 kg
- Overall height: 94 mm
- Overall length: 70 mm
- Overall width: 104 mm

#### Service

- Warranty: 2 year(s)

#### Technical specifications

- Bulb technology: Not applicable
- Mains power: 50 Hz
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: No

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696176788
- Net weight: 0.15 kg
- Gross weight: 0.23 kg
- Height: 11.1 cm
- Length: 7.8 cm
- Width: 10.8 cm



Issue date: 2026-03-21  
Version: 0.351

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)