

PHILIPS

Puled Ground
Spots/Spike 4.6W

myGarden

PULED

black

LED



17481/30/PO



Enjoy a lovely garden with light

This authentic Philips Puled spot light in black adds a charming look to your garden at night. It casts warm white light, bringing your garden to life at night for a family dinner or outdoor get togethers.

Light modes

- Soft warm white light

Match your exterior style

- Designed for outdoor use – water resistant IP44

Designed for outdoors

- High-quality aluminium and real glass

Special characteristics

- Adjustable spot head
- Easy to set up for every application

Design your garden with light

- Decorative outdoor lighting

Highlights

Soft warm white light

Create a cosy atmosphere with warm white light. A smart light that simply adapts to your daily activities

Designed for outdoor use

This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high-quality die-cast aluminium and real glass.

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

Easy to set up

Decorative outdoor lighting

Outdoor lighting can improve the look of your garden or outside space, illuminating eye-catching features, lighting pathways with style or creating the perfect ambience for those memorable evenings with friends and family. That's why Philips has created myGarden, a range of beautiful decorative outdoor lighting with the flair and functionality to help you make the most of your outdoor space in your own style.

Specifications

Design and finishing

- Colour: Black
- Material: Aluminium, Glass

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Defined light beams: Yes
- Dimmable: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden and Patio

Light characteristics

- Colour temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Ground Spots/Spikes
- EyeComfort: No
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 0.584 kg
- Overall height: 105 mm
- Overall length: 97 mm
- Overall width: 97 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture (hidden): 395
- Lumen output bulb included: 395
- Light source equivalent to traditional bulb of: 50
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: Range 220 V–240 V, 50–60 Hz
- Energy class included light source: F
- Fitting/cap: GU10
- Wattage bulb included: 5 W
- Maximum wattage replacement bulb: 5
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class I – Earthed
- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8718696176849
- Net weight: 0.67 kg
- Gross weight: 0.8 kg
- Height: 21 cm
- Length: 12.5 cm
- Width: 12.5 cm



Issue date: 2025-12-06
Version: 0.623

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com