

# PHILIPS

Canaval Ceiling  
Light 18 W

Ceiling Lights

4000K

White

Dimmable; SceneSwitch



32809/31/P3



## One fixture, your switch, three light settings

Philips Canaval LED Ceiling light is a classic white luminaire that fits into any interior, for energy-efficient, high-quality and long-lasting light. Choose your desired brightness for different moods at home with step dimming.

### Ease of use

- Smooth surface finish for easy cleaning

### Light effect

- Even light distribution

### Sustainable light solutions

- Long operating life of up to 15 years

### Advanced LED light

- High light output

### Energy saving

- Built-in LED, as part of the system
- 80% energy saving

### Three light settings

- Change the ambience at a flick of your existing light switch

# Highlights

## Easy to maintain



## Even light distribution



## Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 15,000 hours (which equals 15 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

## High light output

High-quality light with strong light output. The light shines at a beam angle of 40° – the perfect angle for spot lighting.

## Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambience in your home.

## 80% energy saving



Up to 80% energy saving compared to standard incandescent light sources.

## SceneSwitch 3 light settings

Dim your lights without having to use a dimmer with SceneSwitch Brightness Change. Change between three brightness levels with ease using your existing switch.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Colour: White
- Material: Metal, Plastic

**Durability**

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

**Environmental**

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

**Light characteristics**

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous efficacy (rated) (nom.): 116

**Miscellaneous**

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, SceneSwitch

**Other characteristics**

- Lamp current: 150 mA

**Product dimensions and weight**

- Net weight: 0.66 kg
- Overall height: 67 mm
- Overall length: 350 mm
- Overall width: 350 mm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Diameter: 350 mm
- Total lumen output fixture: 2100
- Bulb technology: LED
- Light colour: Cool white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I – Earthed

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696169278
- Net weight: 0.66 kg
- Gross weight: 0.97 kg
- Height: 38.6 cm
- Length: 7.2 cm
- Width: 38.5 cm



Issue date: 2026-04-15  
Version: 0.910

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)