

PHILIPS

Enneper Recessed Light


Recessed Lights

No bulb

white



50181/31/PN



Create the right light style

Philips Enneper recessed spot light is made of high quality material and simple lines that fit every style. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high-quality and long-lasting light.

Special characteristics

- No bulb included
- Easy bulb swap

Designed for your living room and bedroom

- high-quality material
- No dust, no rust

Highlights

No bulb included

This lamp comes without a bulb, which enables you to choose the light output that is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure high-quality and long-lasting light output.

Easy bulb swap

The new easy-to-use ring allows effortless GU10 bulb installation.

high-quality material

This recessed spot is made of high-quality synthetics. This ensures a solid and long-lasting product which will enhance your home for many years to come.

No dust, no rust

The special no dust, no rust surface material of this recessed spot minimises dust-gathering and ensures a long lifetime for your product.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: White
- Material: Synthetic

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Anti-rust anti-dust: Yes
- Dimmable with remote control: No
- Easy bulb swap: Yes
- LED integrated: No
- Made for LED only: Yes
- Remote control included: No

Light characteristics

- Luminous efficacy (rated) (nom.): 100

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.112 kg
- Recessed distance: 100 mm
- Overall height: 42 mm
- Overall length: 90 mm
- Overall width: 90 mm
- Recessed ceiling cutout: 7.0 cm x 7.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: -
- Bulb technology: LED
- Mains power: AC 220-240
- Fixture dimmable: No
- Energy class included light source: bulb not included
- Fitting/cap: GU10
- Wattage bulb included: -
- Maximum wattage replacement bulb: 5.5
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 8718696160367
- Net weight: 0.11 kg
- Gross weight: 0.17 kg
- Height: 158 mm
- Length: 53 mm
- Width: 103 mm



Issue date: 2026-03-21
Version: 0.1135

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com